


CHILLER CONCEPT

CHILL YOUR BOTTLES IN AN INSTANT



Increase your sales

Satisfy and retain your costumers
Attracts new costumers

Cut your cost

More economical than a fridge

Fast and versatile

100% of your references to
the desired temperature



Label will remain dry



Consumption
70W



Easy to use and
maintain



Quiet

TECHNICAL SHEET

Size

Height	85 cm
Width	45 cm
Length	45 cm
Mobility	mounted on 4 wheels



4 wheels

Weight


Empty	45 Kg
In operating condition	70 Kg

Exterior

Frame	Metal
Body	Plastic mold
Color	Black / Burgundy

Capacity

Bottle capacity	3
Location 1 and 2 (traditional bottles 75cl)	Diameter 10,5 cm Depth 46 cm
Location 3 (Magnum)	Diameter 13,5 cm Depth 46 cm



Electronic

3 visual and audible chronometers per location,
indicated by a star (from 3 to 9 minutes)

GENERAL OPERATION

A simple plug is enough.

The containers (example bottle) are inserted in a pocket made of silicone immersed in a stainless steel tank.

The cold is immediately transmitted to the container which cools the contents.

There is no contact between the container and the liquid, the container remains dry.

Liquid doesn't need mixing.

Unique isolation technology allows self sustaining use for more than 12h.

Cold-cooled propylene glycol-based liquid solution based on R404a gas.

STORAGE CONDITIONS

During use, the Chiller must be stored in a normal working environment.

Surrounding temperature <35 ° Celsius

Humidity level <85%

At least 5 cm of ventilation space is required on the lower left and right sides of the Chiller.

MACHINE'S RENEWABLES

Pockets: Silicone-based, they are soft and strong but can tear if misshandled.

The pockets are very easy to change. (2 screws)

The liquid solution does not need to be changed.

There is no evaporation.